

LED Bulb Series



VT-244

HIGHLIGHTS :

WATTS



4

EQ. WATTS



35

LUMINOUS



400

BEAM ANGLE



300

PRODUCT FEATURES

Item No	:	VT-244
SKU Code	:	280
Watts	:	4
EQ. Watts	:	35
Base / holder	:	E27
Voltage	:	AC:220-240V,50Hz
Lumen(lm)	:	400
Color Temperature	:	2700K
Beam Angle	:	300
Commercial type	:	G45
PF	:	>0.4
LED Chip Type	:	Filament-Samsung Chip
CRI	:	>80
Energy rating label	:	A++
Certification	:	EMC,LVD,ROHS
IP Rating Protection Class	:	IP20
Body type	:	Glass
Dimmable	:	No
Life Time	:	20,000 Hours
EAN code	:	3800157633710
Unit size	:	ø45x77mm
Packing details	:	100.00