

## LED Candle Series



### VT-255

#### HIGHLIGHTS :

WATTS



4.5

EQ. WATTS



40

LUMINOUS



470

BEAM ANGLE



200

#### PRODUCT FEATURES

Item No	:	VT-255
SKU Code	:	258
Watts	:	4.5
EQ. Watts	:	40
Base / holder	:	E14
Voltage	:	AC:220-240V,50Hz
Lumen(lm)	:	470
Color Temperature	:	3000K
Beam Angle	:	200
Commercial type	:	C37
PF	:	>0.4
LED Chip Type	:	SMD-Samsung Chip
CRI	:	>80
Energy rating label	:	A++
IP Rating Protection Class	:	IP20
Body type	:	Thermoplastic
Dimmable	:	No
Life Time	:	30,000 Hours
EAN code	:	3800157633680
Unit size	:	ø37x100mm
Packing details	:	200.00