

DS-73xxHQI-K4 SERIES

TurboHD DVR



- HDMI Output Resolution Up to 4K (3,840 x 2,160)
- H.265+/H.265/H.264+/H.264 Main Stream Encoding
- Self-Adaptive HD-TVI/CVBS Signal Input
- Long Distance Transmission over UTP and Coaxial Cable: Maximum of 800 m for 1080p and 1,200 m for 720p HD-TVI Signal
- 4/8/16-ch Synchronous Playback

TurboHD DS-73xxHQI-K4 Series DVRs feature support of HD-TVI, CVBS and IP cameras on up to 16 channels. They offer long transmission distances and feature new important H.265+ compression technology, which improves recording efficiency and reduces data storage costs.

Additionally, the DS-73xxHQI-K4 Series DVRs support advanced analytics such as line crossing, intrusion, scene change detection, people counting, heat map functionality, and Video Quality Diagnostics (VQD).

Available models: DS-7304HQI-K4, DS-7308HQI-K4, DS-7316HQI-K4

