

Product data sheet

Characteristics

NSYCVF54M230MM2

Climasys forced vent. 54 m3/h, 230V, 2 metal grilles and 2 anti-insect filters




Main

Range	ClimaSys
Product name	ClimaSys CV
Product or component-type	Fan
Type of ventilation filter	Anti-insect
Air flow	Free flow rate without filter or grille: 170 m3/h Overall flow rate: 54 m3/h at 50 Hz
Input voltage	230 V 50/60 Hz

Complementary

Height	External: 120 mm
Width	External: 120 mm
Depth	External: 38 mm
Cut-out dimensions	96 x 96 mm
Material	Steel for outlet grille Stainless steel 304L for filter
Colour	Outlet grille: grey RAL 7035
IP degree of protection	IP33
Device composition	1 axial motor 1 power cord 2 anti-insect filter 2 metal louvre

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.