



Main

Range	ClimaSys
Product name	ClimaSys CV
Product or component-type	Fan
Type of ventilation filter	Standard
Air flow	Free flow rate without filter or grille: 170 m3/h Free flow rate with standard filter: 65 m3/h at 50 Hz
Input voltage	230 V 50/60 Hz

Complementary

Height	External: 124 mm
Width	External: 124 mm
Depth	External: 55 mm
Cut-out dimensions	Ø 108 mm
Material	ABS for outlet grille Polyurethane foam for filter
Colour	Outlet grille: black Filter: black
IP degree of protection	IP20
Device composition	1 outlet grille front 1 axial motor 2 protective grille on the front and rear surfaces 1 filter front of axial motor

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**