


Full screen 5.0" smartphone based on Android 7.0 at a very affordable price

VARIETY OF COLORS



- Full screen experience: see more and hold less with 5.0" display with 18:9 aspect ratio. Enjoy the comfort of bezel-less phone.
- Compact design: sleek body and 2.5D curved screen glass ensure gorgeous look. Smartphone is available in golden, red, blue and black color options.
- Updated Android OS version: 7.0 Nougat version with smart battery saving mode Doze and lots of other up-to-date features
- Photography: advanced 8.0MP AF camera with LED-flash ensures excellent clear & vivid images.
- High performance and energy saving: based on quad core processor and 1GB RAM
- Dual SIM: for optimizing budget on calls and Internet

SIM card slot	Dual SIM: WCDMA + GSM
Display	Size: 5.0" Resolution: FWVGA+ (960x480), 18:9 Technology: TN, 2.5D curved screen glass
Processor	SC7731C 1.2GHz quad core
Memory	Built-in: 1GB RAM + 8GB eMMC Expandable: slot for microSD™ card up to 32GB
Power	2000 mAh Li-ion battery
OS	Android 7.0 Nougat
Imaging	Front: 2.0MP with flash Rear: 8.0MP AF with flash

Network	3G WCDMA: 900/2100MHz 2G GSM: 850/900/1800/1900MHz
Connectivity	Bluetooth, Wi-Fi: 802.11b g n USB: microUSB 2.0
Audio	Mic, speakers, 3.5 jack
Built-in devices	GPS, FM
Dimensions	136 x 65 x 9.4 mm
Weight	138g (with battery)
In the box	USB cable, AC charger, screen protective film