


EAO AG

Tannwaldstrasse 88

4600 Olten

Switzerland

Phone: +41 62 286 9111

info@eao.com

Part No. 45-190H.3000.111.401, Keylock Switch


[Specifications](#) | [Bill of Materials](#)

Specifications

Actuator	Keylock switch
Lens Colour	None
Function	2 Pos., maint., key release L/R (KL-KR)
Housing Material	Metal/Plastic
Shape of Handle or Frontring	None
Lock System	RONIS
Key	T254
Key Type	Standard Lock: Ronis T254
Switching Angle	90 Grad (V-Pos)
Contacts	1NO
Terminal	Spring-loaded terminal
Voltage Illumination	None

Mounting Type	Front mounting
Mounting Style	Holder
Environmental Rating	IP66, IP67, IP69K
Industry Standards/Certifications	UL, CSA, VDE, CCC, CE, RoHS
Switching Function	On-Off
Illumination	None
Contact Material	Silver
Termination Style	Spring type
Mechanical Life	1'000'000 switching cycles
AC Voltage	500 V
DC Voltage	500 V
Switching Current	10 A

Bill of Materials

Actuator	45-290H.3000.111
Holder	45-2300.1000.000
Switch Element 1	45-311.1Z40