


**EAO AG**

Tannwaldstrasse 88

4600 Olten

Switzerland

**Phone:** +41 62 286 9111

[info@eao.com](mailto:info@eao.com)

## Part No. 45-190F.3000.113.108, Keylock Switch


[Specifications](#) | [Bill of Materials](#)

### Specifications

Actuator	<a href="#">Keylock switch</a>
Lens Colour	None
Function	3 Pos., maint., key release L/C/R (KL-KC-KR)
Housing Material	Metal/Plastic
Shape of Handle or Frontring	None
Lock System	RONIS
Key	T254
Key Type	Standard Lock: Ronis T254
Switching Angle	2x45 Grad (V-Pos)
Contacts	1NO, 1NO
Terminal	Screw terminal
Voltage Illumination	None

Mounting Type	Front mounting
Mounting Style	Holder
Environmental Rating	IP66, IP67, IP69K
Industry Standards/Certifications	UL, CSA, VDE, CCC, CE, RoHS
Switching Function	On-Off
Illumination	None
Contact Material	Silver
Termination Style	Screw
Mechanical Life	1'000'000 switching cycles
AC Voltage	500 V
DC Voltage	500 V
Switching Current	10 A

## Bill of Materials

Actuator	45-290F.3000.113
Holder	45-2300.1000.000
Switch Element 1	45-311.1Z10
Switch Element 2	45-311.1Z10