

Product data sheet

Characteristics


8536SDO1V02H30S

Non-Reversing Starter Size 2, 3-Pole, Motor Logic SSOLR, Open +Options

Product availability : Stock - Normally stocked in distribution facility



Price* : 1106.00 USD



Main

Product or component type	Starter
Range of product	S
Control circuit	Separate control circuit

Complementary

[Uc] control circuit voltage	110 V AC 50 Hz 120 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	45 A
Poles description	3P
Phase	3 phases
Rated power in HP	10 HP 200 V AC 15 HP 230 V AC 25 HP 460 V AC 25 HP 575 V AC
System Voltage	600 V AC
Control type	No control units
Thermal overload type	Solid state Motor Logic class 10/20
Electrical connection	Screw clamp terminals
NEMA size	2
Height	7.8 in (198 mm)
Depth	4.92 in (125 mm)
Width	4.29 in (109 mm)

Environment

NEMA degree of protection	Not rated (open device)
Product certifications	CSA

NEMA
UL listed

Ordering and shipping details

Category	21192 - 8502,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901807094
Nbr. of units in pkg.	1
Package weight(Lbs)	6.9800000000000004
Returnability	Y
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1545 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
------------------------	---

Contractual warranty

Warranty period	18 months
-----------------	-----------
