

## THC-T230 3 MP EXIR Bullet Camera



### Key Features

- 3 megapixel high-performance CMOS
- Analog HD output, up to 3 MP resolution
- 3.6mm fixed focal lens
- Day/Night switch
- DNR
- Smart IR
- Up to 40 m IR distance
- IP66


## Specifications

<b>Camera</b>	
Image Sensor	3 MP CMOS image sensor
Signal System	PAL/NTSC
Effective Pixels	2052 (H) × 1536 (V)
Min. illumination	0.01 Lux@(F1.2, AGC ON), 0 Lux with IR
Shutter Time	1/25 (1/30) s to 1/50,000 s
Lens	3.6mm
	Field of view : 70.9°(3.6 mm)
Lens Mount	M12
Day & Night	ICR
Angle Adjustment	Pan: 0° to 360°, Tilt: 0° to 180°, Rotation: 0° to 360°
Synchronization	Internal synchronization
Video Frame Rate	1920 × 1536@18fps
HD Video Output	1 analog HD output
<b>General</b>	
Operating Conditions	-40 °C to 60 °C (-40 °F to 140 °F), Humidity: 90% or less (non-condensation)
Power Supply	12 V DC ± 15%
Power Consumption	Max. 4 W
Protection Level	IP67
Material	Metal
IR Range	Up to 40 m
Dimensions	∅ 110 mm × 94.52 mm (∅ 4.33" × 4.35")
Weight	240 g (0.53 lb.)

## Order Model

THC-T230

## Dimensions



## Accessories



DS-1272ZJ-110-TRS  
Wall Mounting Bracket



DS-1275ZJ  
Vertical Pole Mounting Bracket



DS-1276ZJ  
Corner Mounting Bracket



DS-1280ZJ-M  
Junction Box



DS-1281ZJ-S  
Inclined Ceiling Mounting  
Bracket



DS-1H18  
Video Balun