

tesa® 4287

Tensilised strapping tape

tesa® 4287 is a tensilised polypropylene strapping tape with a natural rubber adhesive system.

tesa® 4287 exhibits good tensile strength with low elongation at the same time. The applied product is highly heat and cold resistant.

Main Application

Palletising, belting of electronic components, bundling and closure of shipping cartons.

Technical Data

▪ Backing material	MOPP	▪ Adhesion to steel	4 N/cm
▪ Total thickness	79 µm	▪ Elongation at break	35 %
▪ Type of adhesive	natural rubber	▪ Tensile strength	180 N/cm

Properties

▪ Residue free removal	yes	▪ No discolouration	yes
------------------------	-----	---------------------	-----

For latest information on this product please visit <http://l.tesa.com/?ip=04287>

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.