

50650

## Technical Data

▪ Backing material	PET	▪ Elongation at break	120 %
▪ Total thickness	50 µm	▪ Tensile strength	50 N/cm
▪ Type of adhesive	silicone	▪ Temperature resistance	220 °C
▪ Adhesion to steel	3.3 N/cm		

## Properties

▪ Hand tearability	●	▪ Paint anchorage	●●●●
▪ Anti spotting	●●●●	▪ Sharp colour edge	●●●●
▪ Easy to remove	yes	▪ Conformability	●●●

Evaluation across relevant tesa® assortment: ●●●● very good ●●● good ●● medium ● low

For latest information on this product please visit <http://l.tesa.com/?ip=50650>

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.