




## WLS15XDW0360DSQP

### ▶ WLS15 LOW PROFILE, LOW POWER LED STRIP LIGHT



WLS15 Work Light Strip; Diffused Window; Length:  
360 mm

Voltage: 12 or 24 V dc; Environmental Rating:  
IP66,67

Color: Daylight White

Euro 4-pin 150 mm (6 in) PVC Pigtail

Part Number: 802032

#### CERTIFICATIONS



#### SPECIFICATIONS








<b>Housing Style</b>	Linear Strip
<b>Primary Housing Material</b>	Polycarbonate
<b>Illumination</b>	Yes
<b>Mounting Thread</b>	No Thread
<b>Color Input Control</b>	Individual (One wire/color, same number of colors as input wires)
<b>Number of Colors / Segments</b>	1

<b>Color Option 1</b>	White
<b>Animation Option 1</b>	Solid On
<b>Lumens Color 1</b>	350
<b>Color 1 - Wavelength/Color Temp/Coordinates</b>	5000K (Daylight)
<b>Dimming Option</b>	PWM
<b>Connection Type</b>	Pigtail QD
<b>QD Type/Cable Length</b>	150 mm; M12 (Euro) requires mating cordset
<b>Number of Input Pins/Conductors</b>	4
<b>Supply Voltage</b>	12/24 V dc
<b>Illuminated Dimension (LxWxH or DxH mm)</b>	286.4 x 26.6
<b>Physical Dimensions (LxWxH or DxH mm)</b>	360.0 x 30.6 x 15.5
<b>Environmental Rating</b>	IP66; IP67
<b>Max Op. Temperature (°C)</b>	60
<b>Min Op. Temperature (°C)</b>	-40
<b>Storage Temp (°C)</b>	-40 to 70
<b>Primary Window Material</b>	Polycarbonate Diffused
<b>Secondary Material</b>	Polyamide
<b>Vibration and Mechanical Shock</b>	Vibration 10-55 Hz 1.0 mm p-p amplitude per IEC 60068-2-6, Shock 15G 11 ms duration half sine wave per IEC 60068-2-27
<b>Mechanical Shock</b>	Shock 15G 11 ms duration half sine wave per IEC 60068-2-27
<b>Vibration</b>	Vibration 10-55 Hz 1.0 mm p-p amplitude per IEC 60068-2-6
<b>Feature: Hazardous Area</b>	No
<b>Feature: Audible</b>	No
<b>Feature: Chemical Resistant</b>	No
<b>IO Link</b>	No

<b>Modbus RTU</b>	No
<b>Wireless</b>	No








## RECOMMENDED PRODUCTS

### DOUBLE ENDED CORDSETS

	<p><b>MQDEC-401SS</b></p> <p>Euro-style Quick Disconnect Cable; Double-ended 4-pin Male Connector Straight; 4-pin Female Connector Straight 0.3 m Length; Chrome plated brass coupling nut</p>
	<p><b>MQDEC-403SS</b></p> <p>Euro-style Quick Disconnect Cable; Double-ended 4-pin Male Connector Straight; 4-pin Female Connector Straight 0.91 m Length; Chrome plated brass coupling nut</p>
	<p><b>MQDEC-406SS</b></p> <p>Euro-style Quick Disconnect Cable; 4-pin Straight Connector; 2 m (6.5 ft) Length; Double Ended With 1 Female &amp; 1 Male Connector</p>
	<p><b>MQDEC-412SS</b></p> <p>Euro-style Quick Disconnect Cable; Double-ended 4-pin Male Connector Straight; 4-pin Female Connector Straight 3.7 m Length; Chrome plated brass coupling nut</p>
	<p><b>MQDEC-420SS</b></p> <p>Euro-style Quick Disconnect Cable; Double-ended 4-pin Male Connector Straight; 4-pin Female Connector Straight 6.1 m Length; Chrome plated brass coupling nut</p>
	<p><b>MQDEC-430SS</b></p> <p>Euro-style Quick Disconnect Cable; Double-ended 4-pin Male Connector Straight; 4-pin Female Connector Straight 9.1 m Length; Chrome plated brass coupling nut</p>
	<p><b>MQDEC-450SS</b></p> <p>Euro-style Quick Disconnect Cable; Double-ended 4-pin Male Connector Straight; 4-pin Female Connector Straight 15 m Length; Chrome plated brass coupling nut</p>

### SINGLE ENDED CORDSETS




	<p><b>MQDC-406</b></p> <p>Euro-style Quick Disconnect Cable; 4-Pin Straight Connector; 2 m (6.5 ft) in Length; Nickel-plated Brass Coupling Nut</p>
---	---

	<p><b>MQDC-406RA</b></p> <p>Euro-Style Quick Disconnect Cable; 4-Pin Right-Angle Connector; 2 m (6.5 ft) in Length; Nickel-plated brass coupling nut</p>
	<p><b>MQDC-415</b></p> <p>Euro-style Quick Disconnect Cable; 4-Pin Straight Connector; 5 m (15 ft) in Length; Nickel-plated Brass Coupling Nut.</p>
	<p><b>MQDC-415RA</b></p> <p>Euro-Style Quick Disconnect Cable; 4-Pin Right-Angle Connector; 5 m (15 ft) in Length; Nickel-plated brass coupling nut</p>
	<p><b>MQDC-430</b></p> <p>Euro-style Quick Disconnect Cable; 4-Pin Straight Connector; 9 m (30 ft) in Length; Nickel-plated Brass Coupling Nut</p>
	<p><b>MQDC-430RA</b></p> <p>Euro-Style Quick Disconnect Cable; 4-Pin Right-Angle Connector; 9 m (30 ft) in Length; Nickel-plated brass coupling nut</p>
	<p><b>MQDC-450</b></p> <p>Euro-Style Quick Disconnect Cable; 4-Pin Straight Connector; 15 m (50 ft) in Length; Nickel-plated Brass Coupling Nut</p>
	<p><b>MQDC-450RA</b></p> <p>Euro-Style Quick Disconnect Cable; 4-Pin Right-Angle Connector; 15 m (50 ft) in Length; Nickel-plated brass coupling nut</p>

## ADAPTERS, BRACKETS, CLAMPS AND MOUNTING ACCESSORIES

	<p><b>LMBWLS15</b></p> <p>Bracket: For use with WLS15; Mounting Clip Kit; Contains 3 Brackets</p>
	<p><b>LMBWLS15-150S</b></p> <p>Bracket: For use with WLS15; 150 Degree Rotation; Set of two; Stainless Steel</p>
	<p><b>LMBWLS15MAG</b></p> <p>Bracket: For use with WLS15; Magnetic Mounting Kit; Set of two; Up to 16 lb Pull</p>

## ACCESSORIES

	<b>PSD-24-4</b> DC Power Supply - Desktop Style; Input: 90 -264 V ac 50/60 Hz: 1.8 m (6 ft) US Style outlet plug; Output: 24 V dc 4A: 2 m (6.5 ft) Euro 4-pin Connector; UL Listed Class 2
	<b>LMBWLS15TD</b> Two strips of 3M Dual Lock adhesive
	<b>LMBWLS15TF</b> Two strips of double sided foam urethane tape



Banner Engineering India | Office No. 1001, 10th Floor, Sai Capital, Opp. ICC

Senapati Bapat Road | Pune, 411016 | Contact Us: 08030695482