

Shrink sleeve - WMS 4,8 (15X9)RXL - 0800397

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Shrink sleeve, Roll, white, can be labeled with: THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2: without print, perforated, mounting type: slide on, cable diameter range: 1.6 - 4.8 mm, lettering field size: 15 x 9 mm

Why buy this product

- UL 224 (125°C, 600 V, all tubing)
- CSA.C22.2 No. 198.1 (125°C, 600 V, all tubing)
- The sleeves are pre-assembled for optimum use of material
- The conductor to be marked is simply threaded through the sleeve and fixed by shrinking the sleeve
- The sleeves remain flexible after shrinking
- The shrink sleeves provide additional electrical insulation and mechanical protection for the conductors
- Up to four markers per sleeve are separated by perforations



Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 1 STK |
| GTIN |  4 046356 626644 |
| GTIN | 4046356626644 |
| Weight per Piece (excluding packing) | 1,349.700 g |
| Custom tariff number | 39173200 |
| Country of origin | China |
| Note | Made to Order (non-returnable) |

Technical data

Dimensions

| | |
|----------------|-------------------|
| Length (b) | 15 mm |
| Width (a) | 9 mm |
| Cable diameter | 1.6 mm ... 4.8 mm |

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -55 °C ... 135 °C |
|---------------------------------|-------------------|

Shrink sleeve - WMS 4,8 (15X9)RXL - 0800397

Technical data

General

| | |
|-------------------------------------|-----------------------------|
| Color | white |
| Base element material | polyolefine |
| Type | Shrink sleeve |
| Components | halogen-free |
| Material | Polyolefine |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Printing | without print |
| Number of individual labels | 10000 |
| Number of individual labels per row | 4 |
| Marking mounting type | slide on |

Standards and Regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 24190219 |
| eCl@ss 4.1 | 24190219 |
| eCl@ss 5.0 | 27400401 |
| eCl@ss 5.1 | 27400401 |
| eCl@ss 6.0 | 27400401 |
| eCl@ss 7.0 | 27400401 |
| eCl@ss 8.0 | 27400105 |
| eCl@ss 9.0 | 27400401 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC001530 |
| ETIM 4.0 | EC000217 |
| ETIM 5.0 | EC000217 |
| ETIM 6.0 | EC001530 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39131504 |

Approvals

Approvals

Shrink sleeve - WMS 4,8 (15X9)RXL - 0800397

Approvals


Approvals

CSA / UL Recognized

Ex Approvals

Approval details

| | | | |
|-----|---|---|--------|
| CSA |  | http://www.csagroup.org/services-industries/product-listing/ | 252259 |
|-----|---|---|--------|

| | | | |
|---------------|---|---|---------------|
| UL Recognized |  | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | FILE E 310982 |
|---------------|---|---|---------------|

Accessories

Accessories

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 64-WMSU - 0801360



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., width: 64 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 110-WMSU - 0801358



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., width: 110 mm, color: black
