

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1122190052](#)  
**Status:** **Active**  
**Overview:** Woodhead ArcArrest Connector System  
**Description:** Woodhead ArcArrest 70° Angle Receptacle, Switch-Rated, 30.0A, 480V AC, 3-Pole +Ground, Insulator Keying Position 4

**Documents:**

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E145923

**General**

Product Family Wiring Devices  
 Series [112219](#)  
 IP Rating IP69K  
 NEMA Configuration N/A  
 Overview [Woodhead ArcArrest Connector System](#)  
 Product Literature Order No 987651-4741  
 Product Name ArcArrest  
 Receptacle Type Single  
 Specialty Switch-Rated  
 Type Receptacle  
 UPC 78172559229  
 Woodhead Yes

**Physical**

Flange Yes  
 Flip Lid Yes  
 Gender Female  
 Length 110.30mm (4.340")  
 Locking Blade N/A  
 Net Weight 98.540/g  
 Poles 3

**Electrical**


Cord Type N/A  
 Current - Maximum per Contact 30.0A  
 GFCI No  
 Lighted Connector No  
 Voltage - Maximum 480V AC

**Material Info**

Engineering Number ARC30FAE03

**Reference - Drawing Numbers**

Sales Drawing 1122190052-000



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS Not Reviewed

ELV Not Reviewed

RoHS Phthalates Not Reviewed

**Search Parts in this Series**

[112219 Series](#)