


PRODUCT ATTRIBUTE SHEET

PRODUCT DATA

HARVARD MODEL NO	GDSB06BT40OP	
PRODUCT DESCRIPTION	40W 2.0 BLUETOOTH SOUNDBAR	
PRODUCT CATEGORY	SOUNDBAR	
COLOUR	BLACK	
SUPPLIER MODEL NO	GDSB06BT40OP	
COUNTRY OF ORIGIN	CHINA	
BARCODES	EAN13	5018379111819
	ITF14	05018379111826
COMMODITY CODE		
DUTY RATE %		

PRODUCT SPECIFICATION

<ol style="list-style-type: none"> 1 2.0 channel speaker system 2 Bluetooth streaming 3 Preset audio modes for music, movie and voice 4 RCA aux-in 5 3.5mm line-in 6 Optical in 7 40W RMS 8 9 10 11 12 13 14 15 16 17 18 19 20 	 <p>PLACE GIFT BOX IMAGE HERE</p>
--	---

ACCESSORIES (What's included)

<ol style="list-style-type: none"> 1 3.5MM LINE-IN cable 2 3.5MM LINE-IN to RCA cable 3 RCA to RCA cable 4 Optical cable 5 Remote control 6 Power adaptor 7 Wall mount kit 8 Quick start guide 9 Safety & guarantee booklet 10 	<p>PLACE ACCESSORIES IMAGE HERE</p>
--	-------------------------------------

MARKETING COPY (Features & Benefits)

<ol style="list-style-type: none"> 1 Simple connections 2 With one easy connection, you can effortlessly upgrade the sound on your flat screen TV. 3 Its sleek design and modern look means that it suits any home or style. 4 The Goodmans 40W soundbar makes wireless connectivity options simple with built-in Bluetooth. 5 Immediate hassle free pairing means you can listen to all your favourite music from any one of your compatible devices. 6 Equipped with Line-in, RCA and optical inputs the 40W Bluetooth soundbar is ready for most TV and home audio set-ups 7 We include all the cables you need – meaning you can simply plug in and play as soon as you get home. There's no need for any additional speakers or unsightly wires so you can simply add great sound to your television 8 9 10 	
--	--

PACKAGING AND DIMENSIONS DETAILS FORM

All suppliers as part of any agreement to supply products to Harvard International Limited Group of companies, shall for each product forward Packaging Material details as defined below. Details MUST be forwarded before the product is released for production.

PRODUCT DATA	
HARVARD MODEL NO	GDSB06BT400P
PRODUCT DESCRIPTION	GOODMANS 40W 2.0 BLUETOOTH SOUNDBAR
PRODUCT CATEGORY	SOUNDBAR
COLOUR	BLACK
SUPPLIER MODEL NO	GDSB06BT400P
COUNTRY OF ORIGIN	CHINA

DIMENSIONS & WEIGHTS						
	WIDTH (MM)	HEIGHT (MM)	DEPTH (MM)	NET WEIGHT (KG) (excluding product weight)	GROSS WEIGHT (KG) (including product weight)	
UNIT	815	88	75	1.8		
GIFTBOX	930	140	122	2.6		
OUTER CARTON	995	156	255	4.14	5.70	

PACKING INFORMATION			
GIFTBOX QUANTITY	1		
OUTER CARTON QUANTITY	2		
CONTAINER LOADING	20' FCL	1600	
	40' FCL	3250	
	40' HQ	3800	
	45'		

WASTE INFORMATION				BATTERY INFORMATION			
MATERIAL TYPE	WEIGHT OF GIFTBOX WASTE PACKING (KG)		WEIGHT OF OUTER CARTON WASTE PACKING (KG) (O/C ONLY)		DESCRIPTION	UNIT	REMOTE
	UNIT		OUTER	(PER UNIT)			
PAPER (CARD)	0.510		1.560	0.780	BATTERY TYPE	N/A	Li-Mn Button Cell
GLASS	0.000				MODEL (Name)	N/A	CR2025
ALUMINIUM	0.000				WEIGHT (grams)	N/A	
STEEL	0.000				LIFE (HRS)	N/A	
PLASTIC (INC POLY BAG)	0.070				Volts	N/A	
WOOD	0.000				Capacity (mAh)	N/A	
OTHER	0.000						

TECHNICAL SPECIFICATION											
POWER OUTPUT	WATTS PER SPEAKER	DISPLAY TYPE I.E LCD	DAB Y/N	BLUETOOTH Y/N	CD COMPATIBLE Y/N	USB PORT Y/N	DOCK Y/N	COMPATIBLE DEVICES I.E APPLE, ANDROID	NUMBER OF PRESET STATIONS	AUTO SCAN Y/N	TUNER AM/FM ?
40W RMS	2 x 20W	n/a	N	Y	N	N	N	Y VIA BT	n/a	n/a	N
ALARM FUNCTION Y/N	SNOOZE FUNCTION ?	AUX INPUT Y/N	HEADPHONE SOCKET Y/N	BASS CONTROL Y/N	TREBLE CONTROL Y/N	MAINS OR BATTERY OPERATED?	BATTERY INC Y/N			IN THE BOX (WHAT'S INCLUDED) ?	
N	N	Y	N	N	N	Mains	n/a			3.5MM LINE-IN cable 3.5MM LINE-IN to RCA cable RCA to RCA cable Optical cable Remote control Power adaptor Wall mount kit Quick start guide Safety & guarantee booklet	