

## Basic

Brand Name:	Acer
Environmentally Friendly:	Yes
Graphics Controller	Intel
Manufacturer:	
Graphics Controller Model:	HD Graphics 630
Graphics Memory Accessibility:	Shared
Graphics Memory Technology:	DDR4 SDRAM
HDMI:	Yes
Number of USB 2.0 Ports:	4
Operating System Architecture:	64-bit
Operating System Platform:	Windows
Operating System:	Windows 10 Pro
Optical Drive Type:	DVD-Writer
Processor Manufacturer:	Intel
Processor Model:	i5-7400
Processor Speed:	3 GHz
Processor Type:	Core i5
Product Family:	Veriton ES2710G
Product Type:	Desktop Computer
Standard Memory:	4 GB
Total Hard Drive Capacity:	1 TB
Total Number of USB Ports:	6
VGA:	Yes

## Display & Graphics

Graphics Controller	Intel
Manufacturer:	
Graphics Controller Model:	HD Graphics 630
Graphics Memory Accessibility:	Shared
Graphics Memory Technology:	DDR4 SDRAM
TV Card:	No

## General Information

Brand Name:	Acer
Manufacturer Part Number:	DT.VQEEK.010
Manufacturer Website Address:	<a href="http://www.acer.co.uk">http://www.acer.co.uk</a>
Manufacturer:	Acer, Inc
Product Line:	Veriton
Product Name:	Veriton ES2710G Desktop Computer
Product Series:	ES2710G
Product Type:	Desktop Computer

## I/O Expansions

Number of PCI Express x16 Slots:	1
Number of Total Expansion Slots:	1

## Input Devices

Keyboard Type:	Physical Keyboard
Keyboard:	Yes
Pointing Device Type:	Mouse

## Interfaces/Ports

Audio Line In:	Yes
Audio Line Out:	Yes
HDMI:	Yes
Modem (RJ-11):	No
Network (RJ-45):	Yes
Number of USB 2.0 Ports:	4
Number of USB 3.1 Gen 1 Ports:	2
Total Number of USB Ports:	6
VGA:	Yes

## Memory

Maximum Memory:	32 GB
Memory Card Reader:	No
Memory Standard:	DDR4-2400/PC4-19200
Memory Technology:	DDR4 SDRAM
Standard Memory:	4 GB

## Miscellaneous

Certifications & Standards:	<ul style="list-style-type: none"> <li>• DMI</li> <li>• GS</li> <li>• PC2001</li> <li>• BSMI</li> <li>• VCCI</li> <li>• CE</li> <li>• FCC</li> <li>• CB</li> </ul>
Environmental Certification:	RoHS
Environmentally Friendly:	Yes
Features:	Security Slot
Package Contents:	<ul style="list-style-type: none"> <li>• Veriton ES2710G Desktop Computer</li> <li>• USB Keyboard</li> <li>• USB Mouse</li> </ul>

### Network & Communication

Ethernet Technology:	Gigabit Ethernet
Modem:	No

### Physical Characteristics

Depth:	320 mm
Height:	340 mm
Width:	165 mm

### Power Description

Maximum Power Supply Wattage:	220 W
-------------------------------	-------

### Processor & Chipset

64-bit Processing:	Yes
Cache:	6 MB
Chipset Manufacturer:	Intel
Chipset Model:	H110 Express
Direct Media Interface:	8 GT/s
Maximum Turbo Speed:	3.50 GHz
Number of Processors Installed:	1
Number of Processors Supported:	1
Processor Core:	Quad-core (4 Core)
Processor Generation:	7th Gen
Processor Manufacturer:	Intel
Processor Model:	i5-7400
Processor Speed:	3 GHz
Processor Type:	Core i5

### Software

Operating System Architecture:	64-bit
Operating System Platform:	Windows
Operating System:	Windows 10 Pro

### Storage

Dual-Layer Media Supported:	Yes
Hard Drive Configuration:	1 x 1 TB
Hard Drive Interface:	Serial ATA/600
Hard Drive RPM:	7200
Number of Hard Drives:	1
Optical Drive Type:	DVD-Writer
Optical Media Supported:	DVD-RAM/±R/±RW
Total Hard Drive Capacity:	1 TB