

Tender text

SA-18

Dynamic microphone cartridge,

omnidirectional polar pattern, with protected diaphragm.

Ø 23 mm x 11.5 mm

Specifications:

Polar pattern	omnidir.
Frequency range	100-10,000 Hz
Sensitivity	2.5 mV/Pa
Output impedance	200 Ω
Admiss. ambient temp.	0-40 °C
Dimensions	Ø 23 mm x 11.5 mm
Weight	14 g

Brand: MONACOR

Type: SA-18

Quantity: 1

Packing dimensions: 0.12 x 0.01 x 0.12 m

Gross weight:

Net weight:

Item weight (w/o accessories):