


KEMET, FLLD3-PV, EMI Filters, Three Phase, 520 VAC, 320 A, 300x210x115mm



Dimensions	
L	300mm NOM
W	210mm NOM
H	115mm NOM
L1	120mm NOM
W1	235mm NOM
W2	260mm NOM
U	60mm NOM
X	6mm NOM
Y	25mm NOM
Z	45mm NOM
I	15mm NOM
N	10.5mm NOM
M (Earth)	Threaded Studs M12

Packaging Specifications	
Packaging:	Bulk
Packaging Quantity:	1
Weight:	10 kg

General Information	
Series:	FLLD3-PV
Style:	Chassis Mount
Description:	EMI Filter, Chassis Mount, With Y Capacitor
Features:	High Current
RoHS:	Yes
Qualifications:	IEC/EN 60939, UL 1283

Specifications	
Voltage AC:	520 VAC
Rated Frequency:	50-60 Hz
Current:	320 A (50C)
Rated Temperature:	50C
Temperature Range:	-40/+100C
Climate Category:	40/100/21
Test Voltage DC (P to P):	2250 VDC
Test Voltage DC (P to E):	3000 VDC
Power Loss:	15 W (25C 50 Hz)
Leakage Current:	5 mA (MAX)