


KEMET, FLLD3-PV, EMI Filters, Three Phase, 520 VAC, 1 kA, 350x230x170mm



Dimensions	
L	350mm NOM
W	230mm NOM
H	170mm NOM
L1	145mm NOM
W1	255mm NOM
W2	280mm NOM
U	60mm NOM
X	8mm NOM
Y	40mm NOM
Z	55mm NOM
I	20mm NOM
N	14mm NOM
M (Earth)	Threaded Studs M12

Packaging Specifications	
Packaging:	Bulk
Packaging Quantity:	1
Weight:	17 kg

General Information	
Series:	FLLD3-PV
Style:	Chassis Mount
Description:	EMI Filter, Chassis Mount, With Y Capacitor
Features:	High Current
RoHS:	Yes
Qualifications:	IEC/EN 60939, UL 1283

Specifications	
Voltage AC:	520 VAC
Rated Frequency:	50-60 Hz
Current:	1000 A (50C)
Rated Temperature:	50C
Temperature Range:	-40/+100C
Climate Category:	40/100/21
Test Voltage DC (P to P):	2250 VDC
Test Voltage DC (P to E):	3000 VDC
Power Loss:	75 W (25C 50 Hz)
Leakage Current:	5 mA (MAX)