




# TRIAx

connecting the future



## LTE 4 Way IR Pass Amplifier

Article number: 334022

### Product description:

- Distributes to multiple TV's around the home
- Allows control of Sky Digital receivers when used with Triax Digital Links
- 2 Input 4 Output
- Short circuit protected on each output
- Power on LED
- Screened housing
- F-Connectors
- Easy to mount fixing
- Mains powered
- 9VDC/15mA on outputs

### Specifications

| ORDER INFORMATION                |                 |
|----------------------------------|-----------------|
| EAN Number                       | 5702663340220   |
| CHARACTERISTICS                  |                 |
| Output level IMD 2/IMD 3 @ 60 dB | 93.0 dB $\mu$ V |
| Return Path                      | 5...30 MHz      |
| FREQUENCY                        |                 |
| Frequency range DAB              | 217-230 MHz     |

|                          |   |
|--------------------------|---|
| Frequency range FM       | 87.5-108 MHz  |
| Frequency range          | 87.5-230 / 470-790 MHz  |
| Output frequency range   | 85...790 MHz  |
| Frequency range UHF      | 470-790 MHz   |
| Frequency range BIII/DAB | 85...230 MHz  |
| <b>GAIN</b>              |   |
| Gain                     | 10 +/-2 dB  |
| Noise figure             | <5 dB   |
| <b>ELECTRICAL</b>        |   |
| Impedance                | 75 $\Omega$   |
| <b>OPERATIONAL</b>       |   |
| LED indicator            | Yes   |
| AC Supply voltage        | 230 $\pm$ 10% / 50Hz VAC  |
| <b>CONNECTORS</b>        |   |
| Connector Type           | F-female  |
| Number of inputs         | 2   |
| Number of outputs        | 4   |
| <b>MECHANICAL</b>        |   |
| Colour                   | RAL 7016  |
| Packing QTY              | 1   |
| Net Weight               | 0,485 kg  |
| Tara Weight              | 0,090 kg  |
| Total Weight             | 0,575 kg  |
| Remarks                  | Fully screened within plastic housing >25dB rejection at 821MHz Short circuit protection on outputs |