



SP-7/4SQ

Order No.: 10.3580

Price upon request

PRODUCTINFOS

Universal speaker, 4 W, 4 Ω

- For standard applications in the miniature speaker range
- Sound pressure from approx. 200 Hz on

TECHNICAL SPECIFICATIONS

SP-7/4SQ

Impedance (Z)	4 Ω
Frequency range	f3-17000 Hz
Power rating	4 W
Peak music power output	8 W
Magnet diameter	\varnothing 40 mm
Mounting cutout	\varnothing 61 mm
Mounting depth	25.2 mm

SP-7/4SQ

Mounting hole diameter	Ø 73.5 mm
Width	66.5 mm
Height	66.5 mm
Depth	26 mm
Admiss. ambient temp.	0-40 °C
Weight	90 g
Sales unit	1