



SP-8/4SQ

Order No.: 10.3620

PRODUCTINFOS

Universal speaker, 10 W, 4 Ω

- For standard wide bandwidth applications
- Sound pressure from approx. 100 Hz on

TECHNICAL SPECIFICATIONS

SP-8/4SQ

Impedance (Z)	4 Ω
Frequency range	f3-16000 Hz
Power rating	10 W
Peak music power output	20 W
Magnet diameter	\varnothing 60 mm
Mounting cutout	\varnothing 79 mm
Mounting depth	44.2 mm

SP-8/4SQ

Mounting hole diameter	Ø 105 mm
Dimensions	88.5 x 88.5 x 45 mm
Width	88.5 mm
Height	88.5 mm
Depth	45 mm
Admiss. ambient temp.	0-40 °C
Weight	262 g
Sales unit	1
Type of speaker	3"