

LED Signalleuchten LED Panel Mount Indicators

EINBAUURCHMESSER
MOUNTING HOLE

6 mm

8 mm

12 mm

14 mm


16 mm

19 mm

22 mm

ZUBEHÖR
ACCESSORIES


Außenreflektor ohne Vorwiderstand IP40 / *Prominent (exterior) bezel without resistor IP40*



Part Number	Colour	Typ. Forward Voltage	Typ. Current	Typ. Lumi. Intensity
Hochglanzverchromter Metallreflektor / <i>Satin chrome bezel</i>				
19040003	red	2,0V DC	–	80mcd at 20mA
19040001	green	2,2V DC	–	32mcd at 20mA
19040002	yellow	2,1V DC	–	32mcd at 20mA
19040007	blue	4,5V DC	–	60mcd at 20mcd
1904000W5D	white	3,2V DC	–	2000mcd at 20mcd
Schwarzverchromter Metallreflektor / <i>Black chrome bezel</i>				
19041003	red	2,0V DC	–	80mcd at 20mA
19041001	green	2,2V DC	–	32mcd at 20mA
19041002	yellow	2,1V DC	–	32mcd at 20mA
19041007	blue	4,5V DC	–	60mcd at 20mcd
1904100W5D	white	3,2V DC	–	2000mcd at 20mcd
Mattverchromter Metallreflektor / <i>Matt chrome bezel</i>				
19042003	red	2,0V DC	–	80mcd at 20mA
19042001	green	2,2V DC	–	32mcd at 20mA
19042002	yellow	2,1V DC	–	32mcd at 20mA
19042007	blue	4,5V DC	–	60mcd at 20mcd
1904200W5D	white	3,2V DC	–	2000mcd at 20mcd

Maximale Frontplattenstärke 5,5mm / *Maximum panel thickness 5.5mm*

Außenreflektor mit Vorwiderstand IP67 / *Prominent (exterior) bezel with resistor IP67*



Part Number	Colour	Voltage	Typ. Current	Typ. Lumi. Intensity
Hochglanzverchromter Metallreflektor / <i>Satin chrome bezel</i>				
19040253	red	12V DC	20mA DC	80mcd
19040251	green	12V DC	20mA DC	32mcd
19040252	yellow	12V DC	20mA DC	32mcd
19040257	blue	12V DC	20mA DC	60mcd
19040353	red	24V DC	20mA DC	80mcd
19040351	green	24V DC	20mA DC	32mcd
19040352	yellow	24V DC	20mA DC	32mcd
19040357	blue	24V DC	20mA DC	60mcd
Schwarzverchromter Metallreflektor / <i>Black chrome bezel</i>				
19041253	red	12V DC	20mA DC	80mcd
19041251	green	12V DC	20mA DC	32mcd
19041252	yellow	12V DC	20mA DC	32mcd
19041257	blue	12V DC	20mA DC	60mcd
19041353	red	24V DC	20mA DC	80mcd
19041351	green	24V DC	20mA DC	32mcd
19041352	yellow	24V DC	20mA DC	32mcd
19041357	blue	24V DC	20mA DC	60mcd
Mattverchromter Metallreflektor / <i>Matt chrome bezel</i>				
19042253	red	12V DC	20mA DC	80mcd
19042251	green	12V DC	20mA DC	32mcd
19042252	yellow	12V DC	20mA DC	32mcd
19042257	blue	12V DC	20mA DC	60mcd
19042353	red	24V DC	20mA DC	80mcd
19042351	green	24V DC	20mA DC	32mcd
19042352	yellow	24V DC	20mA DC	32mcd
19042357	blue	24V DC	20mA DC	60mcd

Maximale Frontplattenstärke 5,5mm / *Maximum panel thickness 5.5mm*
Andere Spannungen auf Anfrage / *Other voltages on request*