

# AURELIA® Robust 9.0®

Examination Gloves



<b>96895</b>	(XS)	ø 100	10 x 100
<b>96896</b>	(S)	ø 100	10 x 100
<b>96897</b>	(M)	ø 100	10 x 100
<b>96898</b>	(L)	ø 100	10 x 100
<b>96899</b>	(XL)	ø 100	10 x 100



**Nitrile**



**Powder Free**



**Blue**



**5.5 +/- 0.2 g**



**Finger-Textured**




**5 Years**

Premium quality Blue Nitrile examination gloves that offer greater tensile strength and protection than both Latex and Vinyl.

Nitrile examination gloves offer extra comfort and flexibility.

- 5mil Powder-Free Nitrile
- 9 Newton
- Non-Sterile
- Beaded cuff
- Ambidextrous
- Latex Free
- AQL 1.5

## Sizes & Dimensions



<b>XS</b>	70 ± 10 mm	min. 240 mm
<b>S</b>	80 ± 10 mm	min. 240 mm
<b>M</b>	95 ± 10 mm	min. 240 mm
<b>L</b>	110 ± 10 mm	min. 240 mm
<b>XL</b>	≥ 110 mm	min. 240 mm

## Single wall thickness



- ① min. 0.13 mm
- ② min. 0.10 mm
- ③ min. 0.08 mm

## Physical properties

	Unaged	Aged
Tensile Strength	min. 14.0 MPa	min. 14.0 MPa
Elongation	min. 500 %	min. 400 %
Strength at Break	min. 9N	min. 9N

## Quality Signs & Certificates

89/686/EEC, 93/42/EWG

ISO 9001:2008, ISO 13485, CMDCAS 13485 (SGS)

EN 455 1-4

EN 420 : 2003 + A 1 : 2009

EN 374 2-3, EN 388

EN 1186: Food Contact Approved (SGS)

