

# LED Signalleuchten LED Panel Mount Indicators


LED Signalleuchten für den Einbaudurchmesser von 14mm (+0,2mm) sind mit hellen, verschiedenfarbigen, diffusen 10mm LEDs bzw. Linsen bestückt. Sie sind mit hochglanzverchromten, schwarzverchromten oder mattverchromten Metallreflektoren lieferbar. Der Anschluss erfolgt in der Regel über Flachstecker 2,8 x 0,8mm. Die entsprechenden Flachsteckhülsen finden Sie auf der Zubehör-Seite. Die Montage der LED Signalleuchten erfolgt mittels der mitgelieferten Sprengringe und Muttern.

**Messingflachstecker = Anode (+)**  
**verzinnter Flachstecker = Kathode (-)**

LED panel mount indicators for a 14mm (+0.2mm) mounting hole are manufactured with high brightness coloured diffused 10mm LEDs or lenses. These LEDs or lenses are fitted in high quality satin chrome, black chrome or matt chrome metal bezels, supplied with fixing nut and washer. Connection is usually by faston tab terminals 2.8 x 0.8mm. Suitable crimp connectors can be found on the page for accessories.

**Brass terminals = anode (+)**  
**Tinned terminals = cathode (-)**


## Standardreflektor ohne Vorwiderstand IP40 / Standard bezel without resistor IP40



Part Number	Colour	Typ. Forward Voltage	Typ. Current	Typ. Lumi. Intensity
<b>Hochglanzverchromter Metallreflektor / Satin chrome bezel</b>				
19210000	red	2,0V DC	–	150mcd at 20mA
19210001	green	2,2V DC	–	70mcd at 20mA
19210002	yellow	2,1V DC	–	70mcd at 20mA
<b>Schwarzverchromter Metallreflektor / Black chrome bezel</b>				
19211000	red	2,0V DC	–	150mcd at 20mA
19211001	green	2,2V DC	–	70mcd at 20mA
19211002	yellow	2,1V DC	–	70mcd at 20mA
<b>Mattverchromter Metallreflektor / Matt chrome bezel</b>				
19212000	red	2,0V DC	–	150mcd at 20mA
19212001	green	2,2V DC	–	70mcd at 20mA
19212002	yellow	2,1V DC	–	70mcd at 20mA

Maximale Frontplattenstärke 11mm / Maximum panel thickness 11mm

## Standardreflektor mit Vorwiderstand IP67 / Standard bezel with resistor IP67



Part Number	Colour	Voltage	Typ. Current	Typ. Lumi. Intensity
<b>Hochglanzverchromter Metallreflektor / Satin chrome bezel</b>				
19210250	red	12V DC	20mA DC	150mcd
19210251	green	12V DC	20mA DC	70mcd
19210252	yellow	12V DC	20mA DC	70mcd
19210350	red	24V DC	20mA DC	150mcd
19210351	green	24V DC	20mA DC	70mcd
19210352	yellow	24V DC	20mA DC	70mcd
<b>Schwarzverchromter Metallreflektor / Black chrome bezel</b>				
19211250	red	12V DC	20mA DC	150mcd
19211251	green	12V DC	20mA DC	70mcd
19211252	yellow	12V DC	20mA DC	70mcd
19211350	red	24V DC	20mA DC	150mcd
19211351	green	24V DC	20mA DC	70mcd
19211352	yellow	24V DC	20mA DC	70mcd
<b>Mattverchromter Metallreflektor / Matt chrome bezel</b>				
19212250	red	12V DC	20mA DC	150mcd
19212251	green	12V DC	20mA DC	70mcd
19212252	yellow	12V DC	20mA DC	70mcd
19212350	red	24V DC	20mA DC	150mcd
19212351	green	24V DC	20mA DC	70mcd
19212352	yellow	24V DC	20mA DC	70mcd

Maximale Frontplattenstärke 11mm / Maximum panel thickness 11mm  
Andere Spannungen auf Anfrage / Other voltages on request

EINBAUDURCHMESSER  
MOUNTING HOLE

6 mm

8 mm

12 mm

14 mm

16 mm

19 mm

22 mm

ZUBEHÖR  
ACCESSORIES