




Pocket Audio Generator

VM156


Great little tool
for service, repair,
testing, education,
etc...




SINE



BURST



NOISE




Freq / Mode indicators



Level Adj.



Freq / Mode select
button at the back



Specifications:

- Microprocessor technology
- Digital waveform generation
- Sine wave : 50Hz, 100Hz, 1KHz, 10KHz, 20KHz
- Burst : 50Hz, 100Hz, 1KHz
- Burst mode : 20ms ON, 500ms OFF
- Noise : 32-bit digital noise
- Output level (10Kohm): 0 to 775mV (0dB)
- Outputs : 2 x RCA (cinch)
- Power supply : 2 x CR2016 or CR2025 battery (excl.)
- Dimensions : 86 x 50 x 25 mm