

SC360 - 360° Ceiling Mounted PIR

Features: Dual Element Pyro Sensor, Digital Pulse Count, ASIC Controlled, Power Up Design, Walk Test LED, High RFI & EMI Immunity, Pulse Count 1, 2 Alternate Polarity.



Product Specification

General Specifications

Dual element pyro sensor
High level RFI/EMI protection
Digital pulse count 1 or 2 jumper selectable
LED enabled input & via jumper

Operation Specifications

Alarm period	>2 seconds
Mounting Height	2.4m - 3.5m
Detection Speed	0.3—3ms
Range	360°, 11metre diameter

European Standards:

Electro-magnetic Compatibility (EMC) 89/336/EEC (Amended by 92/31/EEC and 93/68EEC) RoHS

Technical Specification

Plastic housing material	ABS
Dimensions	86mm X 25.50mm in depth
Weight	50g

Order Code

LY15-011-28

Electrical Specification

Operating voltage	9-16Vdc
Operating current	15mA
Alarm contacts	Normally closed dry contacts
Tamper contacts	Normally closed dry contacts (0.5A/24V) with 18Ω resistor in
Storage temperature	-10 to + 50°C

Coverage

