



NEMA SOCKET ELECTRONIC PHOTOCELL KIT

- Thermoplastic construction
 - Electronic operation: improved accuracy over thermal types
 - Supplied complete with mounting bracket and gasket
 - 1500VA or 5 Amp inductive load at 60MFD
 - Max LED load: 1000W
 - Switch on/off at 30/70 lux
- M.O.M: 1 / O.P.Q: 5

Code	Colour	IP Rating
NPCHKIT	Black	IP44

