

PRODUCT FAMILY DATASHEET

OUTDOOR SURFACE SQUARE

Wall and ceiling luminaires with modern design in square shape



AREAS OF APPLICATION

- Outdoor
- Building facades
- Gardens, balconies and other outdoor areas

PRODUCT BENEFITS

- Energy-efficient thanks to LED technology
- 5 years guarantee
- Easy and quick installation
- Homogeneous light output

PRODUCT FEATURES

- Bright and functional outdoor LED luminaires
- Type of protection: IP54
- Die-cast aluminum housing
- Available in two housing colors: white and dark gray
- Diffuser made of opal polycarbonate




TECHNICAL DATA

Product description	Electrical data	Photometrical data	Light technical data	Dimensions & weight				Colors & materials	Temperatures & operating conditions	Lifespan
	Nominal wattage	Luminous flux	Beam angle	Length	Width	Height	Product weight	Product color	Ambient temperature range	Lifespan L70 at 25 °C
O SURFACE SQ 13 W 3000 K IP54 GY 1)	13.00 W	480 lm	100.00 °	202.0 mm	202.0 mm	45.0 mm	910.00 g	Gray	-20...40 °C	30000 h
O SURFACE SQ 13 W 3000 K IP54 WT 1)	13.00 W	600 lm	100.00 °	202.0 mm	202.0 mm	45.0 mm	910.00 g	White	-20...40 °C	30000 h


Product description	Additional product data		Capabilities	Certificates & standards			
	Mounting type	Mounting location	Dimmable	Type of protection	Protection class	Protection class IK (shock resistance)	Photobiological safety group
O SURFACE SQ 13 W 3000 K IP54 GY 1)	Surface	Ceiling / Wall	No	IP54	I	IK06	RG 0
O SURFACE SQ 13 W 3000 K IP54 WT 1)	Surface	Ceiling / Wall	No	IP54	I	IK06	RG 0

Product description	Standards
O SURFACE SQ 13 W 3000 K IP54 GY 1)	CE
O SURFACE SQ 13 W 3000 K IP54 WT 1)	CE


1) Available from February 2018



O SURFACE SQ 13 W 3000 K IP54 GY, O SURFACE SQ 13 W 3000 K IP54 WT



O SURFACE SQ 13 W 3000 K IP54 GY



O SURFACE SQ 13 W 3000 K IP54 WT

EQUIPMENT / ACCESSORIES

- Complete mounting and connecting accessories included

APPLICATION ADVICE

For more detailed application information and graphics please see product datasheet.

LOGISTICAL DATA

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4058075074934	O SURFACE SQ 13 W 3000 K IP54 GY	Shipping carton box 6	470 mm x 255 mm x 215 mm	25.77 dm ³	6094.00 g
4058075074958	O SURFACE SQ 13 W 3000 K IP54 WT	Shipping carton box 6	470 mm x 255 mm x 215 mm	25.77 dm ³	6094.00 g

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
--------------	---------------------	------------------------------	--------------------------------------	--------	--------------

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

REFERENCES / LINKS

For Guarantee see

▶ www.ledvance.com/guarantee

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.