

## Verbatim LED MR16 GU5.3

- GU5.3 Socket
- 12 AC/DCV
- 25,000 hours Lifetime
- 70% Energy Saving
- Luminous Flux: 225 lm
- Equivalent to 20W incandescent bulb

**Product Number** 52020

**General Data**

Lamp Socket GU5.3

**Electric Data**

Wattage (W) 6 W

Wattage Equivalent (W) 20

Voltage (V) 12 V AC/DC

Dimmable no

Power Factor 0.70

Operating Frequency (Hz) 50-60

**Geometric Data**

Length (mm) 44.0

Diameter (mm) 50.0

Weight (g) 42

**Photometric Data**

Luminous Flux (lm) 225 lm

CRI  $\geq 80$

CCT (K) 2700

Luminous Intensity (cd) 400

Beam Angle (°) 25

Lifetime (hrs) 25,000



## Product image



## Application image



## Technical Packaging Details

**Barcode**

023942520207

**EAN 128**

(02)00023942520207(37)0100(91)53

**EAN 14**

50023942520201

**Pack Dimensions(HxWxL)**

75 x 57 x 57 (mm)

**Pack Weight**

65 (g)

**MOQ**

10

**Carton Dimensions (HxWxL)**

611 x 303 x 189 (mm)

**Cartons/Pallet**

3

**Layers/Pallet**

4

**Units/Pallet**

1200

