


















## P PIN 20 1.7 W/2700 G4



Product code 4052899964358

|   |            |
|---|------------|
|    | G4         |
|    | 36.0 mm    |
|    | 14.0 mm    |
|   | –          |
| <b>W</b>  | 1.70 W     |
| <b>lm</b>   | 200 lm     |
|  | 200 lm     |
|  | –          |
|  | 200 lm     |
|  | –          |
| <b>cd</b>   | –          |
| <b>K</b>  | 2700 K     |
| <b>COLOUR</b>   | Warm White |
| <b>R<sub>a</sub></b>  | ≥80        |
| <b>t [h]</b>  | 15000 h    |
|  | No         |
| <b>V</b>  | 12 V       |
| <b>Hz</b>   | –          |

|   |             |
|---|-------------|
|    | 100000      |
|    | 300.00 °    |
|    | < 0.50 s    |
|   | < 0.5 s     |
|  | –           |
| <b>Hg</b>   | 0.0 mg      |
|  | A++         |
|  | 2 kWh/1000h |

