


















P PIN 10 0.9 W/2700 G4



Product code 4058075811959

	G4
	33.0 mm
	12.0 mm
	–
W	0.90 W
lm	100 lm
	100 lm
	–
	100 lm
	–
cd	–
K	2700 K
COLOUR	Warm White
R_a	≥80
t [h]	15000 h
	No
V	12 V
Hz	–

	100000
	300.00 °
	< 0.50 s
	< 0.5 s
	–
Hg	0.0 mg
	A++
	1 kWh/1000h

