

Standard capsules G4 Capsule 12V 20W SV1 0022242



PRODUCT OVERVIEW

IPC Code	0022242
Product name	G4 Capsule 12V 20W SV1
Technology	Halogen
Watt (Rated) (W)	20
Lamp shape	12V Capsule
Cap/Base	G4
Lamp finish	Clear
Fixture rating	Open
General application	Hospitality, Museums & Galleries, Retail, Residential & Consumer
Certifications	EUTIE043
ETIM Class	EC000259
E-number FI	4749224
E-number SE	8355509
E-number Norway	3725780
Luminous flux (lm)	260
Colour temperature (K)	2800
Light colour	Homelight
CRI (Ra)	100
Wattage (W)	20
Average life (Nominal) (h)	2000
Product EAN number	5410288222424

DATA TABLE

General data

IPC Code	0022242
Product name	G4 Capsule 12V 20W SV1
Technology	Halogen
Watt (Rated) (W)	20
Lamp shape	12V Capsule
Cap/Base	G4
Lamp finish	Clear
Fixture rating	Open
General application	Hospitality, Museums & Galleries, Retail, Residential & Consumer
Certifications	EUTIE043

Standard capsules

G4 Capsule 12V 20W SV1
002242

ETIM Class	EC000259
E-number FI	4749224
E-number SE	8355509
E-number Norway	3725780

Optical data

Luminous flux (lm)	260
Luminous flux (Rated) (lm)	260
Colour temperature (K)	2800
Light colour	Homelight
CRI (Ra)	100
Adjustable chromaticity	N
Lumen maintenance at end of nominal life (%)	75

Electrical data

Wattage (W)	20
Starting time (max) (s)	0.01
Warm-up time to 60% of full light (max) (s)	Instant full light
Current (A)	1.667
Mains voltage (V)	12V
Lamp power factor	1
Control gear required	No
No. Of switching cycles before premature failures	8000
Transformer required	Yes
Lamp Energy Label (class)	D
Energy efficiency level	D
kWh per 1000 hours burning time	22

Lifetime data

Average life (Nominal) (h)	2000
Average life (Rated) (h)	2000

Physical data

Max. Lamp Diameter (mm) - D	9
Weight (kg)	0.003

Packaging

Single packaging type	Carton
Product EAN number	5410288222424
Packaging single length / height (cm)	6.6
Packaging single width (cm)	2.5
Packaging single depth (cm)	2.5
DUN14 (inner)	15410288222421
Units per inner package	10
Packaging inner length / height (cm)	6.6
Packaging inner width (cm)	5.1
Packaging inner depth (cm)	12.7


Standard capsules G4 Capsule 12V 20W SV1 0022242

Units per outer package	100
Packaging outer length / height (cm)	27.6
Packaging outer width (cm)	16.1
Packaging outer depth (cm)	14.6

Safety data

Breakage cleaning instructions	Not applicable
Recommendation for disposal at end of life	Not applicable
Special purpose lamp	No
Intended purpose	General lighting
Suitable for household illumination	Yes

TECHNICAL DRAWINGS



Standard capsules
G4 Capsule 12V 20W SV1
0022242

