



DWE46105

1400W 150mm Tuckpointing Shroud Kit NoVolt

Selling Proposition

- Powerful 1400W motor and shroud allow collection of harmful dust during mortar racking applications
- Direct Airlock Compatibility allows quick, secure connection to extraction hose
- Durable steel construction ensures maximum durability in tough site conditions
- Pivoting side door allows mortar removal into internal corners
- Depth adjustment enables correct removal level to be set and maintained
- Dust ejection system removes majority of debris from the air which passes over the motor, preventing abrasion and tracking

Standard Equipment

- 125mm DEWALT Mortar Racking 'Sandwich' Wheel
- Multi-position side handle
- Inner and outer disc flange
- Spanner
- AirLock Adapter

Warranty Specifications

- DEWALT 3 year European PT Guarantee (subject to registration)

Specifications	
Power Input	1400 Watts
No Load Speed	9300 rpm
Max. Disc Diameter	125 mm
Spindle Thread	M14
Weight	2.6 kg
Length	300 mm
Height	80 mm
Hand/Arm Vibration - Grinding	9.4 m/s ²