

# Product information

## 18V Impact Driver Body



### TD127DZ

Battery Type	Lithium-ion
Battery Type	G-Series
Voltage	18 v
Body only machine	1
Charging Time	60 min
Impacts per minute	0 - 3,000 ipm
Machine Screw	M4-M8
Standard Bolt	M5-M14
High Tensile Bolt	M5-M12
No Load Speed	0 - 2,300 rpm
Max Fastening Torque	140 Nm
Noise sound pressure	93 dB(A)
Noise sound power	104 dB(A)
Noise K factor	3 dB(A)
Vibration: Impact tightening of fasteners @ max capacity	2.5 m/sec <sup>2</sup>
Vibration K factor	2 m/sec <sup>2</sup>
Net weight	1.5 kg



**LITHIUM-ION**

- LED Job light with pre-glow function.
- Variable speed control by trigger
- Ergonomic soft grip
- Electric brake
- Forward/reverse rotation

Details correct as of: 2-7-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

[www.makita.com](http://www.makita.com)