

## R18ALH-0 | 18V Cordless Area Light

Article: 5133002339



- Switch between cordless and corded power with the innovative Hybrid technology. Works with any Lithium+ battery or electric power with an extension cord.
- 20W lifetime LED emits up to 1,800 Lumens.
- 360° rotation of the lens and multiple hanging options add versatility.
- Compact design with integrated handle for easy transportation and storage.
- Up to 240 minutes run time as a cordless light with RB18L40 or plug in an extension for AC power.

	R18ALH-0
Voltage (V)	18
Lumens	1800
CRI [Colour Rating Index]	70
CCT [Correlated Colour Temperature]	6000K
Supplied in	Recyclable Carton
Charger supplied	-
No. of batteries supplied	0
Weight [without battery] [Kg]	1.4
Charger included?	No
Power	18V
Article Number	5133002339
Weight with battery pack (kg)	1.9
Weight (kg)	1.9