

Product information

10MM ROTARY DRILL



Satisfying the professional's needs

6413

No Load Speed	0 - 3000 rpm
Input wattage	450 w
Vibration: Drilling	3.5 m/sec ²
Vibration K factor	1.5 m/sec ²
Noise sound pressure	82 dB(A)
Noise sound power	93 dB(A)
Noise K factor	3 dB(A)
Net weight	1.3 kg



- High speed, Ideal for engineering applications
- Soft grip handle
- Keyless chuck
- Variable speed control by trigger
- Forward/reverse rotation

Details correct as of: 2-7-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com