

RPD500-G | 500W Corded Percussion Drill

Article: 5133002244



- Variable speed forward & reverse for total control.
- Compact & lightweight for easy drilling.
- GripZone™ overmould for positive grip and improved comfort.

	RPD500-G
Sound pressure level (dB(A))	95
Sound pressure level uncertainty [dB(A)]	3
Sound power level measured [dB(A)]	106
Sound power level measured uncertainty [dB(A)]	3
Vibration drilling into concrete [m/s ²]	15.6
Vibration drilling into concrete uncertainty [m/s ²]	1.5
No load speed gear 1 (rpm)	3,000
Chuck type	Keyless
Supplied in	Gift box
Charger supplied	-
Weight [without battery] [Kg]	1.6
Power	500W
percussion rate gear 1	0-50,000
Article Number	5133002244
Weight (kg)	1.6
Power input (W)	500
Max drilling steel (mm)	13
Max. drilling wood (mm)	25
Max. drilling masonry (mm)	13
Chuck capacity (mm)	13