

RPD1200-K | 1200W Corded Percussion Drill

Article: 5133002068



- Variable speed forward & reverse for total control.
- Compact & lightweight for easy drilling.
- GripZone™ overmould for positive grip and improved comfort.
- Metal gear housing.
- Metal chuck with auto-spindle lock.
- 2 gears to control the max speed to match different materials and applications.
- Built-in LED light ensures your work piece is always well lit and clearly visible.

	RPD1200-K
Sound pressure level (dB(A))	97.0
Sound pressure level uncertainty [dB(A)]	3.0
Sound power level [dB(A)]	108.0
Sound power level uncertainty [dB(A)]	3.0
Vibration screw driving [m/s ²]	3.9
Vibration screw driving uncertainty [m/s ²]	1.5
Vibration drilling into Metal [m/s ²]	7.4
Vibration drilling into metal uncertainty [m/s ²]	1.5
Vibration drilling into concrete [m/s ²]	15.8
Vibration drilling into concrete uncertainty [m/s ²]	1.5
No load speed gear 1 (rpm)	0-1,200
No load speed gear 2 (rpm)	0-3,200
Chuck type	Keyless
Supplied in	Kitbox
Charger supplied	-
Weight [without battery] [Kg]	3.2
Power	1200W
percussion rate gear 1	0-19,200
percussion rate gear 2	0-51,200
Article Number	5133002068
Weight (kg)	3.2
Power input (W)	1200
Max drilling steel (mm)	8/16
Max. drilling wood (mm)	25/50