

R18ID3-0 | 18V Cordless 3-Speed Impact Driver

Article: 5133002613



- Impact driver ideal for fast tightening and removing of fasteners.
- Powerful impact mechanism delivers up to 4x the power of a drill.
- 3 power levels for wide range of applications, from fitting door hinges to driving decking screws and coach bolts.
- Tri-Beam LED light illuminates the work area and eliminates shadows on bits and fasteners.
- Quick load 1/4" (6.35mm) chuck.
- For best performance and ergonomics we recommend using a 2.5Ah Lithium+ battery which delivers up to 237 screws per charge (4x65mm screws into C24 treated pine).

	R18ID3-0
Sound pressure level (dB(A))	96.0
Sound pressure level uncertainty [dB(A)]	3.0
Sound power level [dB(A)]	107.0
Sound power level uncertainty [dB(A)]	3.0
No load speed (rpm)	0-3,200
Max. torque (Nm)	220
Vibration Impact tightening of fasteners of the maximum capacity of the tool [m/s ²]	17.9
Vibration Impact tightening of fasteners of the maximum capacity of the tool uncertainty [m/s ²]	1.5
Voltage (V)	18
Impact rate (ipm)	0-3,400
Supplied in	Recyclable Carton
Charger supplied	-
No. of batteries supplied	0
Weight [without battery] [Kg]	1.2
Charger included?	No
Power	18V
Article Number	5133002613
Weight with battery pack (kg)	1.7
Weight (kg)	1.7