

R18PD3-0 | 18V Cordless Percussion Drill

Article: 5133002888



- Cordless percussion drill ideal for drilling in wood or metal, driving screws or even drilling in masonry thanks to the hammer function.
- 13mm ratcheting chuck for improved bit gripping strength and durability.
- 2 gears to control the max speed to match different materials and applications.
- 24 torque settings help to drive screws flush every time.
- LED lights up your work area for better visibility.
- For best performance and ergonomics we recommend using a 2.5Ah Lithium+ battery which can drive up to 745 4x32mm screws per charge.

	R18PD3-0
Sound pressure level [dB(A)]	85.6
Sound pressure level uncertainty [dB(A)]	3.0
Sound power level [dB(A)]	96.6
Sound power level uncertainty [dB(A)]	3.0
Vibration screw driving [m/s ²]	0.7
Vibration screw driving uncertainty [m/s ²]	1.5
Vibration drilling into Metal [m/s ²]	1.1
Vibration drilling into metal uncertainty [m/s ²]	1.5
Vibration drilling into concrete [m/s ²]	8.3
Vibration drilling into concrete uncertainty [m/s ²]	1.5
No load speed (rpm)	0-500 / 0-1800
Max. torque (Nm)	50
Torque settings	24
Voltage (V)	18
Battery pack capacity (Ah)	-
Battery type	-
Max. percussion rate (bpm)	6500 / 23400
Supplied in	Recyclable Carton
No. of batteries supplied	0
Weight [without battery] [Kg]	1.3
Charger included?	No
Power	18V
Article Number	5133002888
Weight with battery pack (kg)	1.7