



Gorilla® Grab Adhesive

Product Description: Gorilla Grab Adhesive is a tough, versatile and weatherproof adhesive formulated as an “All Surface, All Purpose” solution. It features fast grab, easy dispensing and is paintable. Its hybrid chemistry provides superior durability even bonding dissimilar materials to withstand indoor and outdoor environments. The premium thick-walled cartridge and removable nozzle provide excellent reusability

Standard Size 290 mL

Physical Properties (Typical)

Bond Strength	2-4 N/mm² (dependent on material type and surface preparation)
Extrusion Rate	200 to 500 g/minute, 0.34 MPa
Skin-Over-Time	10 to 40 minutes, depending on conditions
Specific Gravity, 20°C	1.5
Full cure	24 hours (cure time can change with temperature and humidity conditions)
Service temperature	-40 to 93°C
Application temperature	5 to 38°C, best >10°C
VOC Content	<2% (does not contain solvents)
Hardness	60 Shore A
Tensile strength	1.5 – 1.8 MPa
Elongation at Break	200-300%
Coverage	44 m of 3mm diameter bead 14 m of 5mm diameter bead

Note: The technical information and data found in this data sheet is intended only as representative and should not be used for specification purposes. The information is given in good faith, with tests recommended by PSTC and ASTM and conducted by Quality Assurance and Technical Service Departments. Individual rolls may vary slightly from these averages. Users should determine the suitability of the product for their own purposes by their own tests.