

R18N16G-0 | 18V Cordless 16G Nailer

Article: 5133002222



- AirStrike™ Technology provides cordless convenience, eliminating the need for a noisy compressor, bulky air hose or expensive gas cartridges.
- Fires 16 Gauge (1.6mm) nails from 19 to 65mm long.
- 2 firing modes, full sequential mode for precision and contact actuation mode for rapid fastening.
- Grip-light technology engages LED by grasping the handle.
- Tool less depth of drive adjustment helps protect work surface and allows proper setting of nail heads.
- Dry-fire lockout prevents the tool working without nails loaded.
- Tool less jam release for easy removal of clear nails.

	R18N16G-0
Sound pressure level [dB(A)]	96.5
Sound pressure level uncertainty [dB(A)]	3.0
Sound power level [dB(A)]	107.5
Sound power level uncertainty [dB(A)]	3.0
Vibration nailing [m/s ²]	1.9
Vibration nailing uncertainty [m/s ²]	1.5
Voltage (V)	18
Nail type (mm)	1.6
Supplied in	Recyclable Carton
Charger supplied	-
No. of batteries supplied	0
Weight [without battery] [Kg]	2.7
Charger included?	No
Power	18V
Magazine capacity nails	100
Article Number	5133002222
Weight with battery pack (kg)	3.1
Weight (kg)	3.1
Magazine angle	Straight
Nail capacity	19-65mm