

Product information

115mm Angle Grinder



Satisfying the professional's needs

GA4530R

Bore Diameter	22.23 mm
Max Wheel Diameter	115 mm
Input Wattage	720 w
No Load Speed	11000 rpm
Vibration K factor	1.5 m/sec ²
Vibration: Artificial Wheel	7.5 m/sec ²
Net weight	1.88 - 2.22 kg



STANDARD EQUIPMENT: Grinding wheel, Wrench, Side handle

- Anti-restart function.
- Small gear housing for easy handling and manoeuvrability.
- Machined bevel gears.
- Soft start feature.
- Powerful 720W motor with excellent heat-resistance.
- Ergonomic 20 degree side grip angle.
- Lock-on switch to reduce user fatigue.

Details correct as of: 6-7-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com