

## EAG2000RS | 2000W Corded Angle Grinder, 230mm Disc

Article: 5133000551



- o Full length trigger switch with overmould.
- o 180° multi-directional rotating back handle for improved comfort and control.
- o Tool-less wheel guard for quick and easy adjustment.
- o Two position auxiliary handle with wrench storage.
- o Spindle lock for easy wheel changing.

	EAG2000RS
Sound pressure level (dB(A))	93.0
Sound pressure level uncertainty [dB(A)]	3.0
Sound power level [dB(A)]	104.0
Sound power level uncertainty [dB(A)]	3.0
Vibration level [m/s <sup>2</sup> ]	8.5
Vibration uncertainty [m/s <sup>2</sup> ]	1.5
Bore size (mm)	22
No load speed (rpm)	6,000
Supplied in	Kitbox
Weight [without battery] [Kg]	6
Power	2000W
Spindle size	M14
Article Number	5133000551
Weight (kg)	6.0
Power input (W)	2000
Disc diameter (mm)	230