



## DWE315KT

### Multi-cutter filaire

#### Selling Proposition

- Quick accessory change & adjustment, no Hex Key required
- Superior Ergonomics
- 0 - 22,000 opm Variable Speed Trigger for ultimate control
- Oscillating Angel 1.6°
- Sanding Platen included
- Universal Adaptor included

#### Standard Equipment

- Oscillating Wood with Nails Blade
- Oscillating Fastcut Wood Blade
- Oscillating Wood Detail Blade
- Oscillating Semi Circle Wood Blade
- Oscillating Semi Circle Grout Removal Blade

#### Warranty Specifications

- DEWALT 3 year European PT Guarantee (subject to registration)

Specifications	
Battery chemistry	
Voltage	
Battery Capacity	
Power Output	300 Watt
Power Output	170 Watt
Oscillations per Minute	0 - 22,000
Switch type	Trigger / Variable Speed
Tool free Accessory Fitment	Yes