

Product information

18V MULTI TOOL LXT



DTM50Z

Battery Type	Lithium-ion
Battery Quantity (3.0 Ah)	1
Voltage	18 v
Oscillation Angle	3.2 °
Oscillations per Minute	6000 - 20000
Vibration K factor	1.5 m/sec ²
Vibration: Cutting Metal	5 m/sec ²
Vibration: Cutting Wood	9.5 m/sec ²
Vibration: Chiselling	7.5 m/sec ²
Vibration: Sanding	2.5 m/sec ²
Net weight	1.8 - 2.2 kg



STANDARD EQUIPMENT: Hex wrench

- Thumb On/Off switch, positioned for ease of use when holding body of machine.
- Hex wrench holder on body.
- Variable speed control dial.
- Dust extraction attachment.
- Accessories can be installed at 30° increments, across 360°
- Uses OIS interface.

Details correct as of: 9-7-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com