

0 601 5A1 001 – GST 12V-70

Material number	0 601 5A1 001	0 601 5A1 070
EAN	3165140711463	3165140711470
1 x jigsaw blade T 144 D, Speed for Wood available separately as set of 3: 2 608 630 560	✓	✓
1 x jigsaw blade T 308 B, Extra-clean for Wood available separately as set of 3: 2 608 663 750	✓	✓
2 x battery GBA 12V 2.0Ah 1 600 Z00 02X		✓
Anti-splinter guard	✓	✓
Cardboard box	✓	
Dust extraction set	✓	✓
Glide shoe	✓	✓
L-BOXX 102 1 600 A00 1RP		✓
L-BOXX inlay	✓	✓
Quick charger GAL 1230 CV 1 600 A01 16B		✓
Packaging dimensions (width x length x height)	208 x 335 x 105 mm	360 x 440 x 120 mm
Battery voltage	12.0 V	12.0 V
Weight incl. battery	1,5 kg	1,5 kg
Battery capacity		2,0 Ah

Technical data

Technical data

Stroke rate at no load	1.500 – 2.800 spm
Stroke height	18 mm
Mitre cuts	0–45 °
Battery voltage	12 V

Cutting depth

Cutting depth in wood	70 mm
Cutting depth in aluminium	3 mm
Cutting depth in metal	3 mm

Noise/vibration information

Sound pressure level	77 dB(A)
Sound power level	88 dB(A)
Uncertainty K	3 dB



Sales information

Positioning

- Extremely compact and lightweight 12 volt professional cordless jigsaw

User benefit incl. Reason to believe

- Extremely compact, lightweight cordless jigsaw for perfect handling and manoeuvrability in curves
- High performance: fast sawing progress and long battery runtime
- Grip position is exceptionally close to the cutting line, thus allowing especially precise cutting

