

Product information

18V Jigsaw Body



Satisfying the professional's needs

JV183DZ

Battery Type	Li-ion
Battery Type	G-Series
Voltage	18 v
Body only machine	1
Charging Time	60 min
Capacity in Steel	6 mm
Capacity in Wood	65 mm
Strokes per Minute	0 - 2,900 spm
Stroke Length	18 mm
Noise sound pressure	82 dB(A)
Noise sound power	93 dB(A)
Noise K factor	3 dB(A)
Vibration: Cutting Chipboard	7.0 m/sec ²
Vibration: Cutting Sheet Metal	4.5 m/sec ²
Vibration K factor	1.5 m/sec ²
Net weight	2 kg



LITHIUM-ION

- Change lever for 3 orbital settings and straight cutting.
- Rigid aluminium base bevels 0 to 45 degrees left and right.
- Electric brake
- Bayonet (Universal) Shank Jigsaw Blade
- Connectable to dust extractor
- Compact & Lightweight
- Variable speed trigger control.

Details correct as of: 9-7-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com